


## Plug GL-438...

In-line, Ø 4 mm, with spring-loaded MULTILAM for self-assembly of test leads. With retractable sleeve to prevent accidental touching.

### Various types of connection:

GL-438-L: Soldered connection

GL-438: Screw connection



Order No.	Type	Rated voltage/current	Cable (A)		*Standard colors
64.9701-*	GL-438	AC 30 V/32 A DC 60 V/32 A	PVC TPE Ø 3.9 mm SIL Ø 3.9 mm	2.5 mm <sup>2</sup>	Ni 21 22 23 24 25 29
64.2010-*	GL-438-L	AC 30 V/32 A DC 60 V/32 A	PVC TPE Ø 3.9 mm SIL Ø 3.9 mm	2.5 mm <sup>2</sup>	Ni 21 22 23 24 25 29

### Component parts

64.2040-*	KT-GL-438	Connection sleeve
64.2030	LS-GL-438	Plug suitable for GL-438
64.2020	LS-GL-438-L	Plug suitable for GL-438-L



Assembly instructions MA170

[www.staubli.com/electrical](http://www.staubli.com/electrical)